

Dromex



CUT FOOD GLOVE



55LF

EN 388: 20XX



454X

EN 407:2004



X1XXXX



Description

Dromex® 55LF food grade gloves consist of a sanitized lightweight 100% Dromex® CUT5 fibre, providing protection against high heat, cut and abrasion with an extended cuff for added protection for the wrist. The construction of the gloves allows dexterity and excellent air circulation keeping hands dry and comfortable. 55LF is ambidextrous, lint free and UV resistant when exposed to light. For use in the food processing industry, for boning, carving, fish filleting, meals preparation and food handling applications.

Contact heat protection of the glove is based on the temperatures at which the wearer will feel no pain for at least 15 seconds and at a level 1 contact temperature of 100°C.

Special Instructions

Although the manufacturer has examined these gloves under the system for ensuring quality of production by means of monitoring and inspection, we recommend that all gloves should be thoroughly inspected before use to ensure no damage is present.

None of the materials or processes used in the manufacture of these products are known to be harmful to the wearer. The gloves and information contained herein are designed to accommodate the basic safety requirements and standards for Personal Protective Equipment.

Actual conditions of use cannot be directly simulated in a test environment, therefore it is the responsibility of the user and not the manufacturer or supplier to determine the suitability for intended use.

Compliance & Conformity

Complies with the requirements of CE type examinations EN 420 for innocuousness, EN 388 for compliance with directive 89/686/EEC Mechanical Risks (4,5,4,X) and EN 407:2004 Thermal Risks for Heat and Flame (X1XXXX). ANSI/ISEA 105:2016, American National Standards for Hand Protection, Mechanical Hazards.

Quality System conforms to ISO 9001:2008 and environmental management system ISO 14001:2015 system certificates or acceptable equivalent.

Specifications

Style: Ambidextrous lightweight sanitized glove
 Liner: 100% Dromex® Cut5
 Palm: 1mm ± 5 % 100% Dromex® Cut5
 Back: 1mm ± 5 % 100% Dromex® Cut5
 Cuff: ± 15cm Cuff
 Mass: 45g per glove (size 11)

Packaging, Storage & Obsolescence


Packed individually, sold as 120 units per carton for shipping. Store in a cool, dry place. Stored correctly, the gloves physical properties will not change for up to three years.



Cleaning & Maintenance

Gloves should not be left in a contaminated condition if re-use is intended especially if potential hazards exist. Before removal from the hands excess contaminant should first be removed from the gloves. Should this not be possible, it is advisable to ease left and right hand gloves off using the gloved hand and remove the gloves without the contaminant contacting the bare hands.

The gloves may then be decontaminated as indicated below:



100% Dromex® Cut5 gloves have proven that dry cleaning as well as laundering are suitable cleaning methods. We recommend that no bleaching or oxidising ingredients or any fabric softeners be used. Recommended washing temperature is between 40°C and 60°C (104~140°F) with mild detergents.

The drying process may cause felting on the fabric surface. Drying temperature should not exceed 70°C (158°F). There is no remarkable impact on cut resistance during the normal life cycle of a glove. Depending on glove construction, staining and cleaning method, the differences in shrinkage, yarn strength and colour may occur.

In order to maximise the glove life cycle, we recommend the mildest possible cleaning conditions in terms of temperature, chemicals and cycle duration.

Disposal

All industrial waste should be disposed of correctly according to local regulations and good disposal practice. Gloves should be disposed of considering the hazardous substances they were used for. Please consider recycling.

Sizes Available


7-11

Code	Size	Palm Length
55LF-7	XS/S	98mm (±2mm)
55LF-8	S/M	100mm (±2mm)
55LF-9	M/L	105mm (±2mm)
55LF-10	L/XL	108mm (±2mm)
55LF-11	XL/XXL	111mm (±2mm)

** As per the EN420 standard, actual measurement of gloves are determined by the manufacturer, taking into account the behaviour of the glove material, its thickness (such as leather gloves, PVC gloves etc), elasticity and the intended use.*

** Sizing charts only serve as a guide. Sizes and measurements are for reference only. In order to make an informed decision, always try on the gloves as each glove features a unique construction to accommodate a wearer's preferences.*

Measurement Guide



Materials



1. Sanitized glove
2. 15cm cuff

Disclaimer

Dromex reserves the right to make changes without further notice to any products herein to improve function, design or reliability and validity. Dromex does not assume any liability arising out of the application or use of any product described herein. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.

www.dromex.co.za

Latest update: 06/11/2023