

Dromex



GNYLON GLOVE



GNYLON

Description

Dromex® GNYLON, ambidextrous, nylon gloves with dust and lint retardant properties keeps hands clean and free from dust.

The GNYLON glove is thin, washable, eliminates finger prints and reduces perspiration on your palms and being a synthetic fibre, resists moulds and fungi. Suitable for use in applications such as inspections, component and motor assembly, rendering products free from dust and scratches.

Special Instructions

Although the manufacturer has examined these gloves under the system for ensuring quality of production by means of monitoring and inspection, we recommend that all gloves should be thoroughly inspected before use to ensure no damage is present.

None of the materials or processes used in the manufacture of these products are known to be harmful to the wearer. The gloves and information contained herein are designed to accommodate the basic safety requirements and standards for Personal Protective Equipment. Actual conditions of use cannot be directly simulated in a test environment, therefore it is the responsibility of the user and not the manufacturer or supplier to determine the suitability for intended use.

Compliance & Conformity

Performs equivalent to EN 420 for innocuousness, EN388 for Mechanical Risks (3,1,3,1) for compliance with directive 89/686/EEC. Quality System conforms to ISO 9001:2008.

Specifications

Style:	Ambidextrous nylon gloves
Liner:	Nylon
Palm:	0,34 mm ± 5%
Back:	0,34 mm ± 5%
Cuff:	Composite knitted wrist
Mass:	42 ± g Per pair (size 10)

Sizes Available

8-10

Packaging, Storage & Obsolescence

Packed in individual polybags and sold a 120 pairs per carton for shipping. Store in a cool, dry, dark place.


Stored correctly, the gloves physical properties will not change for up to three years.



Cleaning & Maintenance

Gloves should not be left in a contaminated condition if re-use is intended especially if potential hazards exist. Before removal from the hands excess contaminant should first be removed from the glove. Should this not be possible, it is advisable to ease left and right hand gloves off using the gloved hand and remove the gloves without the contaminant contacting the bare hands.

The gloves may then be decontaminated as indicated below.



Dromex® GNYLON gloves have proven that dry cleaning as well as laundering are suitable cleaning methods. We recommend that no bleaching or oxidising ingredients or any fabric softeners be used. Recommended washing temperature is up to 40°C with mild detergents. The drying process may cause felting on the fabric surface. Drying temperature should not exceed 70°C (158°F).

There is no remarkable impact on cut resistance during the normal life cycle of a glove however, depending on glove construction, staining and cleaning method, the differences in shrinkage, yarn strength and colour may occur.

Disposal

All industrial waste should be disposed of correctly according to local regulations and good disposal practice. Gloves should be disposed of considering the hazardous substances they were used for. Please consider recycling.

