


Dromex



POLYURETHANE COATED NYLON GLOVES

EN 388: 2003



4131



SUPERLITE

Description

Dromex® Superlite PU (polyurethane coated) nylon gloves, reinforces the black Micro foam palm and provides superior dexterity and sensitivity, adding comfort and durability. Suitable for electronic assembly, computer assembly, automotive assembly and small, fine/ precise component handling applications.

Special Instructions

Although the manufacturer has examined these gloves under the system for ensuring quality of production by means of monitoring and inspection, we recommend that all gloves should be thoroughly inspected before use to ensure no damage is present.

None of the materials or processes used in the manufacture of these products are known to be harmful to the wearer. The gloves and information contained herein are designed to accommodate the basic safety requirements and standards for Personal Protective Equipment. Actual conditions of use cannot be directly simulated in a test environment, therefore it is the responsibility of the user and not the manufacturer or supplier to determine the suitability for intended use.

Compliance & Conformity

Complies with the requirements of CE type examinations EN 420 for innocuousness and EN 388 for compliance with directive 89/686/EEC Mechanical Risks (4,1,3,1).

Quality System conforms to ISO 9001:2008.

Specifications

Style: PU (Polyurethane) dipped palm and fingers
Liner: Nylon
Palm: PU coated mm 0,7mm ± 5 %
Back: Nylon 0,6 mm ± 5 %
Cuff: Elasticated nylon
Mass: 25 ± g per pair

Sizes Available

8-11

Packaging, Storage & Obsolescence

Superlite gloves are packed in individual sealed plastic packets and 120 pairs per carton for shipping. Store in a cool, dry place. Stored correctly, the gloves physical properties will not change for up to three years.



Cleaning & Maintenance

Gloves should not be left in a contaminated condition if re-use is intended especially if potential hazards exist. Before removal from the hands excess contaminant should be removed from the gloves.

Should this not be possible, it is advisable to ease left and right hand gloves off using the gloved hand and remove the gloves without the contaminant contacting the bare hands.

The gloves may then be decontaminated with a mild detergent solution, then rinsed with clean water and air dried.

This is an anti-static glove therefore contaminants not removed during cleaning can affect the anti-static properties of the glove.

Disposal

All industrial waste should be disposed of correctly according to local regulations and good disposal practice. Gloves should be disposed of considering the hazardous substances they were used for.

Please consider recycling.

Materials



1. PU dipped palm & fingers
2. Elasticated cuff

Marking