

Dromex




ACTIFRESH NITRILE COATED GLOVES



DH0911A

EN 388:2003



4121

Description

Dromex® 0911A full knuckle and palm coated nitrile gloves provide hands with excellent grip in wet and dry environments. The Sanitized treatment suppresses the reproduction of microbes, such as bacteria and fungi and hinders both the unpleasant odours as well as material damage from mildew.

The cotton liner provides sensitivity and dexterity. The nitrile coating protects the hand from high abrasion and cut hazards.

The cotton blend interlock lining knit wrist cuff secures the glove firmly to the users' wrist and keeps dirt out of the glove.

Suitable for applications of light fabrication, general assembly and material handling machining, packaging and maintenance.

Special Instructions

Although the manufacturer has examined these gloves under the system for ensuring quality of production by means of monitoring and inspection, we recommend that all gloves should be thoroughly inspected before use to ensure no damage is present.

None of the materials or processes used in the manufacture of these products are known to be harmful to the wearer. The gloves and information contained herein are designed to accommodate the basic safety requirements and standards for Personal Protective Equipment. Actual conditions of use cannot be directly simulated in a test environment, therefore it is the responsibility of the user and not the manufacturer or supplier to determine the suitability for intended use.

Compliance & Conformity

Complies with the requirements of CE type examinations EN420 for innocuousness, EN388 for Mechanical Risks (4,1,2,1). Quality System conforms to ISO9001:2008.

Specifications

Style: Full knuckle and palm coated nitrile gloves
 Liner: Cotton Interlock liner
 Palm and back: Nitrile coated 0,7 mm ± 5%
 Cuff: ± 2mm Composite knitted wrist
 Mass: ± 63 g Per pair (size 12)


Packaging, Storage & Obsolescence

The standard packaging for the gloves are as follows. The gloves are not packed in individual bags. The gloves are packed in bundles in a polybag. The polybag glove bundles are placed in cardboard cartons suitable for transportation and storage. Stored correctly, the gloves physical properties will not change for up to three years.



Cleaning & Maintenance

Gloves should not be left in a contaminated condition if re-use is intended especially if potential hazards exist. Before removal from the hands excess contaminant should first be removed from the glove. Should this not be possible, it is advisable to ease left and right hand gloves off using the gloved hand and remove the gloves without the contaminant contacting the bare hands. The gloves may then be decontaminated as indicated below.



In order to maximise the glove life cycle, we recommend the mildest possible cleaning conditions in terms of temperature, chemicals and cycle duration.

Due to a wide variety of possible constructions and combinations with other materials we recommend to always consult your professional cleaning service to determine the best suitable cleaning method.

Disposal

All industrial waste should be disposed of correctly according to local regulations and good disposal practice. Gloves should be disposed of considering the hazardous substances they were used for. Please consider recycling.

Sizes Available

Code	Size	Palm Length
DH0911A-9	M/L	95mm (±5mm)
DH0911A-10	L/XL	100mm (±5mm)
DH0911A-11	XL/XXL	105mm (±5mm)
DH0911A-12	XXL/XXXL	110mm (±5mm)

* As per the EN420 standard, actual measurement of gloves are determined by the manufacturer, taking into account the behaviour of the glove material, its thickness (such as leather gloves, PVC gloves etc), elasticity and the intended use.

* Sizing charts only serve as a guide. Sizes and measurements are for reference only. In order to make an informed decision, always try on the gloves as each glove features a unique construction to accommodate a wearer's preferences.

Marking

Measurement Guide



Materials



1. Wing thumb
2. Fully coated fingers & palm
3. Wrist cuff