


Dromex



GFREEZER



GFREEZER



Description

Dromex® GFREEZER, high visibility, fluorescent orange, thermoplastic PVC (Poly Vinyl Chloride) coated multi-layered lined gloves provides the hands with protection against cold temperatures and mechanical hazards.

These gloves are liquid proof and provides resistance against light chemical contact.

The sandy microdot finish on the glove also provides added grip and excellent abrasion protection for both wet and dry applications.

The multi-layered liner consists of cotton, foam and jersey fabric, keeps the hand warm, soft, comfortable and dry, whilst the double coated PVC layer provides a high mechanical resistance level.

The Gauntlet cuff design, allows ventilation and quick removal of the glove.

This glove is suitable for applications of handling in cold storage, fishing and outdoor environments.

This PVC coating will function well between temperatures of -50°C and 66°C.

Special Instructions

Although the manufacturer has examined these gloves under the system for ensuring quality of production by means of monitoring and inspection, we recommend that all gloves should be thoroughly inspected before use to ensure no damage is present.

None of the materials or processes used in the manufacture of these products are known to be harmful to the wearer. The gloves and information contained herein are designed to accommodate the basic safety requirements and standards for Personal Protective Equipment. Actual conditions of use cannot be directly simulated in a test environment, therefore it is the responsibility of the user and not the manufacturer or supplier to determine the suitability for intended use.

Compliance & Conformity

Complies with the requirements of CE type examinations EN 420 for innocuousness, EN 388 for Mechanical Risks (4,1,2,2), EN 511 for protection against cold (111).

Performs equivalent to the standard of EN 374-2 and EN 374-3, Protective gloves against chemicals and micro-organisms.

Specifications

Style:	Fluorescent, 30cm, fully coated, thermal PVC glove with Gauntlet cuff
Liner:	Interlock cotton with foam
Palm:	1 mm ± 5%
Back:	1 mm ± 5%
Cuff:	Gauntlet cuff
Mass	292 ± g per pair (size 10)

Sizes Available

10/L


Packaging, Storage & Obsolescence

Packed in individual polybags and sold as 72 pairs per carton for shipping. Store in a cool, dry, dark place. Stored correctly, the gloves physical properties will not change for up to three years.



Cleaning & Maintenance

Gloves should not be left in contaminated condition if re-use is intended especially if potential hazards exist. Before removal from the hands excess contaminant should first be removed from the glove. Should this not be possible, it is advisable to ease left and right hand gloves off using the gloved hand and remove the gloves without the contaminant contacting the bare hands. The gloves may then be decontaminated as indicated below.





- Dromex® G-Freezer gloves have proven that dry cleaning as well as laundering are suitable cleaning methods.
- We recommend that no bleaching or oxidising ingredients or any fabric softeners be used.
- Recommended washing temperature is up to 40°C with mild detergents.
- In order to maximise the glove life cycle, we recommend the mildest possible cleaning conditions in terms of temperature, chemicals and cycle duration.
- Due to a wide variety of possible constructions and combinations with other materials we recommend to always consult your professional cleaning service to determine the best suitable cleaning method.
- The drying process may cause felting on the fabric surface. Drying temperature should not exceed 70°C (158°F).

There is no remarkable impact on cut resistance during the normal life cycle of a glove, however depending on glove construction, staining and cleaning method, the differences in shrinkage, weight loss, yarn strength and colour may occur.

Disposal

All industrial waste should be disposed of correctly according to local regulations and good disposal practice. Gloves should be disposed of considering the hazardous substances they were used for. Please consider recycling.

Marking



1. Wing thumb
2. Micro-dotted hand surface
3. Four layers of insulation:
 - Special PVC dipped
 - Cotton interlock
 - Foam insulation
 - Fleeced cotton